

MANUAL DRY ADDITIVE FEEDER

USC's manual dry additive feeder is equipped with stirring arms at the bottom of the hopper, providing continuous agitation while the new dispersion screen (on drum models) provide more accurate and complete coverage as it sifts product onto seed.

FEATURES & ADVANTAGES

- AT500 mount has a 2" diameter, 1' auger for metering.
- Drum mount has 2" diameter, 4' auger for metering.
- Dispersion screen, calibration port, mounting stand and treater door all included.
- Hand/Off/Auto control toggle; auxiliary cord for auto control from treater.
- Digital screen with 10 turn dial for precise motor control.
- Includes 0.9 cubic foot galvanized hopper.
- Auger provides consistent and accurate coverage.
- Includes 90V DC variable speed motor.
- Operates off 120V.

The simple design offers quick and easy calibration, while the 90V variable speed motor provides variable flow ranges, maximizing versatility.

The manual dry additive feeder works on the AT500H and all drum treaters.



MANUAL DRY ADDITIVE FEEDER

MANUAL DRY ADDITIVE FEEDER DIMENSIONS

